



Prismatic™ 2

Multi-Species Gas Analyzer

GASES & CHEMICALS

CEMS

ENERGY

SEMI & HB LED

ATMOSPHERIC

LAB & LIFE SCIENCE

The Prismatic™ 2 features:

- Simultaneous detection of up to four species
- Wide dynamic range
- No calibration required
- Low Cost of Ownership
- Easy to use and install all-in-one solution

With the Prismatic™ 2 laser-based, multi-species trace gas analyzer, Tiger Optics takes a quantum leap forward. With a combined electronics and sensor module that can simultaneously measure multiple analytes in a wide variety of background gases, the Prismatic™ 2 offers precise analysis over a vast dynamic range. You can select multiple species of interest from a sizable and growing detection list, including CH₄, H₂O, CO, CO₂, NH₃ and H₂S.

The Prismatic™ 2 provides a critical tool for use in a variety of applications in both research and industrial settings where continuous, on-line gas monitoring is essential. The ability to measure from parts-per-million to parts-per-trillion of multiple analytes

enables extensive research in gaseous applications at laboratories, from national metrology institutes to fuel-cell hydrogen QC labs.

Our proven CRDS technology offers absolute accuracy, with no external calibration required. Our customers worldwide prize our instruments for their precision, stability, exceptionally low Cost of Ownership, vast dynamic range, rapid speed of response and ease of use & installation, among other attributes. By providing an affordable, yet highly sensitive means to measure multiple trace species in gases, the Prismatic™ 2 offers a compelling choice for many gas analysis applications.

Tigeroptics

21ST CENTURY SPECTROSCOPY

Prismatic™ 2

Multi-Species Gas Analyzer



Performance	
Operating range	See table on next page
Detection limit (LDL, 3σ/24h)	See table on next page
Precision (1σ, greater of)	± 0.5% or 1/3 of LDL
Accuracy (greater of)	± 4% or LDL
Speed of response	< 5 minutes to 95% (in 4-channel operation)
Environmental conditions	10°C to 40°C 30% to 80% RH (non-condensing)
Storage temperature	-10°C to 50°C
Gas Handling System and Conditions	
Wetted materials	316L stainless steel (corrosive gas version optional) 10 Ra surface finish
Gas connections	1/4" male VCR inlet and outlet
Leak tested to	1 x 10 ⁻⁹ mbar l / sec
Inlet pressure	20 – 125 psig (2.4 – 9.6 bara)
Flow rate	< 1 slpm (gas dependent)
Sample gases	Inert gases, hydrogen and oxygen
Gas temperature	Up to 60°C

Dimensions	H x W x D [in (mm)]
Electronics unit and sensor	12.25 x 17.50 x 29.65 (311 x 445 x 753)
Weight	
Standard sensor	70.5 lbs (32.0 kg)
Electrical	
Alarm indicators	User programmable setpoints (1 per channel), Form C relays
Power requirements	90 – 240 VAC, 50/60 Hz
Power consumption	400 Watts max.
Signal output	0–5 VDC analog Isolated 0–20 mA or 4–20 mA
User interfaces	10.4" LCD touchscreen PS/2 mouse and keyboard 10/100 Base-T Ethernet 4 USB ports, RS-232

Prismatic™ 2

Multi-Species Gas Analyzer

Performance in N ₂ or CDA:	Range	LDL (3σ)	Precision (1σ) @ zero
Methane (CH ₄)	0 – 10 ppm	0.75 ppb	0.25 ppb
Ammonia (NH ₃)	0 – 15 ppm	1.1 ppb	0.4 ppb
Moisture (H ₂ O)	0 – 50 ppm	5 ppb	2 ppb
Hydrogen Sulfide (H ₂ S)	0 – 1000 ppm	40 ppb	15 ppb
Carbon Monoxide (CO)	0 – 1000 ppm	100 ppb	35 ppb
Carbon Dioxide (CO ₂)	0 – 2000 ppm	150 ppb	50 ppb

Performance in He:	Range	LDL (3σ)	Precision (1σ) @ zero
Methane (CH ₄)	0 – 6 ppm	0.5 ppb	0.2 ppb
Moisture (H ₂ O)	0 – 10 ppm	1.0 ppb	0.4 ppb
Carbon Monoxide (CO)	0 – 800 ppm	90 ppb	30 ppb
Carbon Dioxide (CO ₂)	0 – 1600 ppm	130 ppb	45 ppb

Performance in Ar:	Range	LDL (3σ)	Precision (1σ) @ zero
Methane (CH ₄)	0 – 9 ppm	0.7 ppb	0.25 ppb
Moisture (H ₂ O)	0 – 20 ppm	2.0 ppb	0.7 ppb
Carbon Monoxide (CO)	0 – 800 ppm	80 ppb	30 ppb
Carbon Dioxide (CO ₂)	0 – 1600 ppm	120 ppb	40 ppb

Performance in O ₂ :	Range	LDL (3σ)	Precision (1σ) @ zero
Methane (CH ₄)	0 – 9 ppm	0.7 ppb	0.25 ppb
Moisture (H ₂ O)	0 – 25 ppm	3 ppb	1.0 ppb
Carbon Monoxide (CO)	0 – 800 ppm	85 ppb	30 ppb
Carbon Dioxide (CO ₂)	0 – 1700 ppm	130 ppb	45 ppb

Prismatic™ 2

Multi-Species Gas Analyzer

Performance in H ₂ :	Range	LDL (3 σ)	Precision (1 σ) @ zero	MDL for fuel-cell hydrogen analysis*
Methane (CH ₄)	0 – 10 ppm	0.75 ppb	0.25 ppb	1 ppb
Ammonia (NH ₃)	0 – 6 ppm	0.8 ppb	0.3 ppb	1 ppb
Moisture (H ₂ O)	0 – 50 ppm	5 ppb	2 ppb	4 ppb
Hydrogen Sulfide (H ₂ S)	0 – 1000 ppm	40 ppb	15 ppb	30 ppb
Carbon Monoxide (CO)	0 – 1200 ppm	120 ppb	40 ppb	100 ppb
Carbon Dioxide (CO ₂)	0 – 3000 ppm	200 ppb	70 ppb	200 ppb

*Method detection limit (MDL) for fuel-cell hydrogen analysis is determined using U.S. EPA 40 CFR Part 136 Appendix B; for more information on fuel cell applications see our special brochure [Advanced Spectroscopic Solutions for Fuel-Cell Hydrogen Analysis](#)
Contact us for additional analytes and matrices.
U.S. Patent # 7,277,177