



HALO H2

Trace-Level Hydrogen Analyzer

GASES & CHEMICALS

CEMS

ENERGY

SEMI & HB LED

ATMOSPHERIC

LAB & LIFE SCIENCE

Designed for trace-level hydrogen analysis, the HALO H2 offers:

- Low parts-per-billion (ppb) detection capability
- Extremely fast speed of response
- Wide dynamic range
- Absolute measurement (freedom from need for calibration gases)
- Low maintenance and cost of ownership
- Direct measurement in many matrices, including oxygen

Leading Choice for Ultra-high Purity Gas Users


Detect gas quality upsets before they damage your process. Using Tiger Optics' HALO H2 hydrogen analyzer, you can verify H₂ impurity levels with part-per-billion accuracy, drift-free stability and instantaneous response. You will find our system exceptionally easy and fast to install, and effortless to maintain, with built-in zero verification. Its robust design—free of moving parts—results in an analyzer

that has a high Mean Time Between Failure (MTBF) rate and a very low Cost of Ownership (CoO).

With its patented catalytic conversion technique, utilizing a minute amount of oxygen to cleanly and safely convert hydrogen to moisture, the HALO H2 offers a fully laser-based solution for continuous quality control of your process.

HALO H2

Trace-Level Hydrogen Analyzer



Performance		Dimensions	H x W x D [in (mm)]
Operating range	See table on next page	Standard sensor	8.73 x 19.0 x 23.6 (222 x 483 x 599)
Detection limit (LDL, 3 σ /24h)	See table on next page	Weight	
Precision (1 σ , greater of)	\pm 0.75% or 1/3 of LDL	Standard sensor	45 lbs (20.4 kg)
Accuracy (greater of)	\pm 4% or LDL	Electrical and Interfaces	
Speed of response	< 3 minutes to 95%	Platform	Max series analyzer
Environmental conditions	10°C to 40°C 30% to 80% RH (non-condensing)	Alarm indicators	2 user programmable 1 system fault Form C relays
Storage temperature	-10°C to 50°C	Power requirements	100 – 240 VAC, 50/60 Hz
Gas Handling System and Conditions		Power consumption	450 Watts max.
Wetted materials	316L stainless steel 10 Ra surface finish	Signal output	Isolated 4–20 mA
Leak tested to	1 x 10 ⁻⁹ mbar l / sec	User interfaces	5.7" LCD touchscreen 10/100 Base-T Ethernet USB, RS-232, RS-485 Modbus TCP (optional)
Gas connections	1/4" male VCR	Data storage	Internal or external flash drive
Sample inlet pressure	10 – 125 psig (1.7 – 9.6 bara)	Certification	CE Mark
Sample flow rate	0.5 slpm (\pm 20%)		
Sample gases	Most inert matrices		
Gas temperature	Up to 60°C		
Utility gas supply*	see below for required gas ~15 sccm, 20 – 125 psig		

Standard Model (requires 1% O₂, 99% N₂ mixture or CDA utility gas)

Performance, H ₂ :	Range	LDL (3 σ)	Precision (1 σ) @ zero
In Nitrogen	0 – 500 ppm	8 ppb	3 ppb
In Argon	0 – 200 ppm	6 ppb	2.0 ppb
In Helium	0 – 125 ppm	4 ppb	1.5 ppb
In Neon	0 – 140 ppm	4 ppb	1.5 ppb

CDA Model (requires pure N₂ utility gas)

Performance, H ₂ :	Range	LDL (3 σ)	Precision (1 σ) @ zero
In Clean Dry Air (CDA)	0 – 5000 ppm	80 ppb	30 ppb

*Utility gas supply purity requirements: <10 ppm H₂O and H₂ impurities

Contact us for additional analytes and matrices.

U.S. Patent # 7,277,177 · U.S. Patent # 7,255,836

Tiger Optics, LLC

275 Gibraltar Road, Horsham, PA 19044
Phone: +1 (215) 656 4000 · Fax: +1 (215) 343 7168
sales@tigeroptics.com · www.tigeroptics.com



Tigeroptics
a Process Insights Brand

4/2022